

Watch

VARTA WATCH BATTERIES



| IEC | VARTA REF | EAN | | Sys | Voltage | BLIST/BOX |
|--------------------|-----------|------------------|---------------|---------------------------------|-------------|-----------|
| VARTA WATCH | | BOX OF 10 | | | | |
| SR43 | V301 | 301.101.111 | 4008496245369 | Watch V301 Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |
| SR44 | V303 | 303.101.111 | 4008496245420 | Watch V303 Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |
| SR48 | V309 | 309.101.111 | 4008496245451 | Watch V309 Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |
| SR67 | V315 | 315.101.111 | 4008496245550 | Watch V315 Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |
| SR62 | V317 | 317.101.111 | 4008496245611 | Watch V317 Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |
| SR64 | V319 | 319.101.111 | 4008496245628 | Watch V319 Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |
| SR65 | V321 | 321.101.111 | 4008496245857 | Watch V321 Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |
| --- | V329 | 329.101.111 | 4008496245864 | Watch V329 Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |
| --- | V335 | 335.101.111 | 4008496101467 | Watch V335 Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |
| --- | V337 | 337.101.111 | 4008496362110 | Watch V337 Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |
| --- | V339 | 339.101.111 | 4008496245871 | Watch V339 Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |
| --- | V341 | 341.101.111 | 4008496245888 | Watch V341 Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |
| SR42 | V344 | 344.101.111 | 4008496245901 | Watch V344 Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |
| --- | V346 | 346.101.111 | 4008496101481 | Watch V346 Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |
| SR42 | V350** | 350.101.111 | 4008496245697 | Watch V350** Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |
| SR44 | V357** | 357.101.111 | 4008496245710 | Watch V357** Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |
| SR58 | V361** | 361.101.111 | 4008496261697 | Watch V361 Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |
| SR58 | V362 | 362.101.111 | 4008496245727 | Watch V362 Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |
| SR60 | V364 | 364.101.111 | 4008496245734 | Watch V364 Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |
| SR69 | V370** | 370.101.111 | 4008496261710 | Watch V370 Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |
| SR69 | V371 | 371.101.111 | 4008496245918 | Watch V371 Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |
| SR68 | V373 | 373.101.111 | 4008496245925 | Watch V373 Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |
| SR66 | V377 | 377.101.111 | 4008496245932 | Watch V377 Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |
| SR63 | V379 | 379.101.111 | 4008496245949 | Watch V379 Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |
| SR55 | V381 | 381.101.111 | 4008496245956 | Watch V381 Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |
| SR41 | V384 | 384.101.111 | 4008496245642 | Watch V384 Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |
| SR42 | V386** | 386.101.111 | 4008496245659 | Watch V386** Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |
| SR58 | V389** | 389.101.111 | 4008496245673 | Watch V389** Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |
| SR54 | V390 | 390.101.111 | 4008496245680 | Watch V390 Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |
| SR55 | V391** | 391.101.111 | 4008496245789 | Watch V391** Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |
| SR41 | V392** | 392.101.111 | 4008496245796 | Watch V392** Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |
| SR48 | V393** | 393.101.111 | 4008496245819 | Watch V393** Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |
| SR45 | V394 | 394.101.111 | 4008496245826 | Watch V394 Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |
| SR57 | V395 | 395.101.111 | 4008496245833 | Watch V395 Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |
| SR58 | V396** | 396.101.111 | 4008496245741 | Watch V396** Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |
| SR59 | V397 | 397.101.111 | 4008496245765 | Watch V397 Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |
| SR57 | V399** | 399.101.111 | 4008496245772 | Watch V399** Silver 1,55V Bls 1 | Silver 1,55 | 10 / 100 |

(**) High drain

VARTA BLOCK BATTERIES



| IEC | VARTA REF | EAN | | | Volt | mAh | Dimensions |
|------------------------------|-----------|---------------|---------------|--------------------------------|------|-------|------------------|
| VARTA BLOCK BATTERIES | | | | | | | |
| 4R25 | 430 | 430.101.111 | 4008496171385 | Spring coils – veren – ressort | 6 | 9000 | 67 x 115 x 67 |
| 4R25 | 420 | 420.101.111 | 4008496203314 | Screw – visse | 6 | 9000 | 235 x 270 x 150 |
| 4R25 | 431 | 431.101.111 | 4008496171392 | spring coils – veren – ressort | 6 | 10000 | 67 x 115 x 67 |
| 6F100 | 439 | 439.101.111 | 4008496204250 | block | 9 | 5000 | 65,5 x 79,5 x 52 |
| 4R25-2 | 540 | 540.101.111 | 4008496165629 | zinc carbon | 6 | 19000 | 130 x 120 x 70 |
| 4LR25-2 | 435 | 435.101.111 | 4008496493999 | Alkaline | 6 | 33000 | 136 x 125 x 73 |
| --- | 99034 | 99034.504.491 | 4008496584147 | Ni-MH pack 4 Watt Accu Lantern | 4,8 | 2200 | 50 x 28 x 28 |